
STATUS INNOVATIONS EN

# FRESKO VACUUM CONTAINERS

User manual

### **COMPOUND PARTS AND MATERIALS**







Fill the container up to 1.5 cm under the top edge. Make sure the valve is lifted and close the container.



Press the valve in flat position. The container is now airtight.



Place the pump around the valve and repeatedly pull the handle. Optimal vacuum is created when you feel slight resistance in the pump.



To open, pull the valve upwards to release vacuum and open the lid.

#### NOTES:

- Vacuum pack only food at room temperature or cold.
- Before first use, wash the containers and lids.
- Make sure that the edge of the container and lid are clean and dry.
- Fresko containers can be vacuum sealed with any Status' vacuum pump.
- microwave safe (max. 2 min. without the lid)
- dishwasher safe (top rack only)
- freezer safe (up to -20 °C)

# Developed and produced in Slovenia, EU.

## Available:

- individually in volumes: 0.5 L, 0.9 L, 1.4 L and 2.3 L;
- in 4-piece set: all 4 volumes in one colour (mint, lilac or salmon);
- in 5-piece set: all 4 volumes in one colour (mint, lilac or salmon) and manual vacuum pump;
- in 5-piece set: all 4 volumes in one colour (mint, lilac or salmon) and battery vacuum pump BVP 50.

innovations

The entire life cycle of our products is envisioned and realized at Status – from **development**, through **production**, **marketing**, **and sales**, to the **service centre**. As our customers you represent the first and the last quality control point as we constantly strive to adapt our products to your needs. We are working hard to ensure that the **Status Innovations** brand is synonymous with quality, efficient and user-friendly products. Our range includes **products for storing food in vacuum as well as without vacuum**, **utensils for food preparation and cooking**, **and other household products**. Our range of products continues to expand.